




Always check the website for the most updated specifications: www.americh.com











All bathtub dimensions are  $\pm 1/2''$ .

# **Builder Series**



**Platinum Series** 







Combination


(pump and blower location only)



























- ACCESS PANEL (MINIMUM 16" X 20")

## **INSTALLATION TIPS**

- Install according to Owner's Manual and local codes.
- Airbath III units may be 11/2" 21/2" higher than stated.
- Any whirlpool or Airbath<sup>®</sup> unit requires an access panel.
- Hot water supply should be 65-75% of tub capacity or greater.
- · Always consult your local plumber for recommendations as installations will vary.
- Cut-out dimensions: Americh recommends waiting until the actual unit is received.
- The combination of multiple systems and options may require components to stick out and/or be remotely installed in the field.

#### **DIMENSIONS**

66" x 44" x 22" (1676 x 1118 x 559 mm) Whirlpool Operating Gallons = 60 (Liters = 227) Gallon to Overflow = 75 (Liters = 284)

**MATERIAL:** Acrylic (All Americh Standard Colors)

TUB FLOOR: Textured **UNDERMOUNT:** Yes

- Advise Americh when ordering to ensure there are no issues with deck mounted controls.
- · Always take dimensions directly from the unit.

## **ELECTRICAL REQUIREMENTS**

Americh recommends one 20 amp ground fault circuit interrupter (GFCI) for each power supply provided with the bathtub.

## STANDARD EQUIPMENT:

Adjustable Feet

#### **OPTIONAL ACCESSORIES**

- Chromatherapy\*
- Grab Bars: 9" \*
- High Density Insulation\*
- iBath Sound System
- Inline Heater (whirlpool only)
- Jets: Additional or Rotary\*
- Lo Profile Tub Edge
- Ozone System (whirlpool and/or Airbath only)
- Pillows: 12" \*
- Remote Control Upgrade (select series only)
- Serenity Soak (tub only)
- Syllent Pump with Heated Air\*
- Thermal Comfort System (TCS must be at opposite end if used with VSM)
- Trim Kit Upgrade\*
- Vibro Sonic Massage (VSM must be at opposite end if used with TCS)
- Waste & Overflows Upgrades
  - Cable Drive Waste & Overflow\*
  - PVC Waste & Overflow<sup>+</sup>

## (\*) Standard on Platinum Series

(+) Standard on Luxury Series

## **CODES AND COMPLIANCE**

Americh products meet or exceed the following standards:

- Underwriters Laboratories (UL)
- Underwriters Laboratories Canada (cUL)
- Canadian Standards Association (CSA)
- ANSI Z124.1 ANSI A112-19.7
- ANSI A112.19.8

Contact Americh for additional approvals.

