



#### OPERATION OF QUICK CONNECT FITTINGS




Pushing tube in before pulling it out helps to release tube



WaterSentry® Plus Filter System

#### ELECTRICAL

Furnished with plug-in, 3-wire grounding type service cord. Standard 120 volt, 60 Hz, singlephase. Install 120-volt receptacle, rated at 15-amp minimum, to receive 3-wire parallel blade grounding type male plug. These products are designed to operate on 20 psi to 105 psi supply line pressure. Simultaneous operation of both bubblers on a bi-level unit may not be possible depending on water supply pressure. If simultaneous operation is desired, please ensure a minimum of 65 psi supply.



#### LEGEND:

- A: Recommended water supply location, 3/8" O.D. unplated copper tube connect stub 1-1/2" (38mm) out from wall shut off valve by others not furnished.
- B: Recommended location for waste outlet, 1-1/2" O.D. drain.
- C: 1-1/2" Trap not furnished.
- D: Electrical supply (3) wire recessed box
- E: Insure proper ventilation by maintaining 6" (152mm) min. clearance from cabinet louvers to wall
- F: 7/16" Bolt holes for fastening unit to wall.

Note : New Installations Must Use Ground Fault Circuit Interrupter (GFCI). It is highly recommended that the circuit be dedicated and the load protection be sized for 20 amps.

\* Adult ADA requirement. 24" (609mm) for Child ADA. Adjust other measurements accordingly.

In keeping with our policy of continuing product improvement, Halsey Taylor reserves the right to change product specifications without notice. Please visit [Halseytaylor.com](http://Halseytaylor.com) for the most current version of Halsey Taylor product specification sheets. This specification describes a Halsey Taylor product with design, quality, and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.